ACCESSORIES & INSTALL KITS



MaxCell field professionals have over twenty years of experience installing cable in the network construction industry. Since 1999, we have developed proven installation techniques specifically designed for MaxCell. The installation kits below are costeffective, reusable and tested to be the most efficient means for MaxCell installations.

MXCIK11

(Pictured Above)

This kit is a single 2,500 lb swivel with an outside diameter of .875" and is designed for use in installing single and multiple packs of our MaxCell product.

(Pictured Below)

This kit contains (3) 2,500 lb swivels with an outside diameter of .875" each and (1) 2-way chain harness. Designed for installing single or multiple packs of MaxCell attached to (1) swivel and a rope, tape or cable attached to a second swivel. The 3rd swivel acts as a parent swivel that attaches the main pull line to the chain harness. This kit allows for different products to be placed simultaneously with the MaxCell product while helping to reduce the number of twists in the conduit structure.

This kit contains (4) 2,500lb swivels with an outside diameter of .875" each and (1) 3-way chain harness. Designed for installing single or multiple packs of MaxCell attached to (1) swivel while the 2nd or 3rd swivel can be attached to either a rope, tape and/or cable. The 4th swivel acts as a parent swivel that attaches the main pull line to the chain harness. This kit allows for the installation of a rope or two cables to be placed simultaneously with the MaxCell product while helping to reduce the number of twists in the conduit structure. In addition, MaxLube pulling lubricant is recommended for all installations to further reduce pulling tensions.



